

52PL4G9 | US2:52PL4G9



30mm Command/52, Chrome Finish Heavy Duty, Watertight/Oiltight Complete Metal Unit Illuminated Indicator Light Transformer type, 120V AC Incandescent Lamp, BA9s Plastic Lens, Amber UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards

List Price

Customer Price

DataSheet in PDF

Download

Service & Support (Manuals, Certificates, FAQs...)

Download

> Image gallery and data for M-CAD and E-CAD (1) (1)

Product data Further Product Information

Product

Article Number (Market Facing Number)	52PL4G9   US2:52PL4G9
Product Description	30mm Command/52, Chrome Finish Heavy Duty, Watertight/Oiltight Complete Metal Unit Illuminated Indicator Light Transformer type, 120V AC Incandescent Lamp, BA9s Plastic Lens, Amber UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards

Product family	> Ordering Data Overview
Product Lifecycle (PLM)	PM300:Active Product

Price data

Price Group	N65
List Price	
Customer Price	
Metal Factor	None

Delivery information

Export Control Regulations	AL : N / ECCN : EAR99
Standard lead time ex-works	1 Day/Days
Net Weight (lb)	0.066 lb
Product Dimensions (W x L x H)	Not available
Packaging Dimension	0.311 x 0.154 x 0.154
Package size unit of measure	in
Quantity Unit	1 Piece
Packaging Quantity	1

Additional Product Information

EAN	Not available
UPC	662643314526
Commodity Code	8531800050
LKZ_FDB/ CatalogID	CC-IC10
Product Group	4649
Country of origin	Mexico
RoHS Compliance	not available
Returnable	Yes
Obligation Category for taking back electrical and electronic equipment after use	No obligation to take back electrical and electronic equipment after use

Classifications

	Version	Classification
UNSPSC	15	39-12-15-34