


52AAENC1 | US2:52AAENC1



Lamp 52AAENC1-120V_2.5w_transpa

List Price > Show prices

Customer Price > Show prices

Additional Services For this product we can offer services like Spare Part Delivery/Repair/Exchange. You have currently no rights to enter the Service Web Shop for that.
> For further information & to order this service, please contact your local Spares&Repair Partner

Image similar

DataSheet in PDF [Download](#)

Service & Support (Manuals, Certificates, FAQs...) [Download](#)

> Image gallery and data for M-CAD and E-CAD (1) (1)

Product data Further Product Information

Product	
Article Number (Market Facing Number)	52AAENC1 US2:52AAENC1
Product Description	Lamp 52AAENC1-120V_2.5w_transpa
Product family	> Ordering Data Overview
Product Lifecycle (PLM)	PM300:Active Product
Price data	
Price Group	N67
List Price	> Show prices
Customer Price	> Show prices
Metal Factor	None
Delivery information	
Export Control Regulations	AL : N / ECCN : EAR99
Standard lead time ex-works	1 Day/Days
Net Weight (lb)	0.11 lb
Product Dimensions (W x L x H)	Not available
Packaging Dimension	0.543 x 0.681 x 0.016
Package size unit of measure	in
Quantity Unit	1 Piece
Packaging Quantity	1
Additional Product Information	
EAN	Not available
UPC	783087765863
Commodity Code	8536509035
LKZ_FDB/ CatalogID	CC-IC10
Product Group	4647
Country of origin	Mexico
Compliance with the substance restrictions according to RoHS directive	not available
Returnable	Yes
WEEE (2012/19/EU) Take-Back Obligation	No
REACH Art. 33 Duty to inform according to the current list of candidates	> Reach Information

Classifications		
	Version	Classification
eClass	5.1	27-37-12-81
eClass	6	27-37-92-13
eClass	7.1	27-37-92-13
eClass	8	27-37-92-13
eClass	9	27-37-92-13
eClass	9.1	27-37-92-13
ETIM	5	EC002024
ETIM	6	EC002024
ETIM	7	EC002024
IDEA	4	5210
UNSPSC	15	39-12-22-16

Buy product

Quantity 1 Piece

[Add to cart](#)

Frequently bought together:



> [3RT20151AK61](#) |

3RT20151AK61
Power contactor, AC-3 7 A, 3 kW / 400 V 1 NO, 110 V AC, 50 Hz 120 V, 60 Hz, 3-pole, Size S00, screw terminal



> [3RT20151BB41](#) |

3RT20151BB41
Power contactor, AC-3 7 A, 3 kW / 400 V 1 NO, 24 V DC 3-pole, Size S00 screw terminal



> [3RT20161AK61](#) |

3RT20161AK61
Power contactor, AC-3 9 A, 4 kW / 400 V 1 NO, 110 V AC, 50 Hz, 120 V 60 Hz, 3-pole, Size S00 screw terminal



> [3SU10500AB400AA0](#) |

3SU10500AB400AA0
Pushbutton, 22 mm, round, metal, shiny, green, pushbutton, flat momentary contact type



> [3SU10501BA200AA0](#) |

3SU10501BA200AA0
Mushroom pushbutton, 22 mm, round, metal, shiny, red, 40 mm, latching, Pull-to-unlatch mechanism