



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 3-Pole, 240VAC are Circuit Protection Molded Case Circuit Breakers. Type: BL Application: Electrical Distribution Standard: UL 489 Voltage Rating: 240V Amperage Rating: 60A Frequency Rating: 400HZ Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 3P

number of poles	3
suitability for operation	Electrical Distribution
continuous current rated value	60 A
supply voltage frequency rated value	400 Hz
product brand name	SIEMENS
type of electrical connection	BOLT-ON
depth [in]	4 in
design of the product	BL
height [in]	3 in
width [in]	3 in
standard	UL 489

last modified:

1/6/2021 