

Model No. 00832



Model No. 00834



Model No. 00838



Carrying Cases

Padded Nylon "Grab N Go" cases, made of tough durable nylon, enables VOM to be stored for quick field use ... test leads remain in panel jacks.

Thick padding protects meter.

Available in yellow (00832) and black (00834) and Orange (00838) for 260 series or similar size meters; (00836) for smaller models.

Roll-Top case (00248) made from thermoset phenolic with roll down front panel is used only on models 260-8, 8P or model 270-5.

Model No. 00836



Model No. 00248



Carrying Cases Test Equipment Accessories

Molded Plastic Case

Foam insert protects meter, plastic case resists scratching and scarring.

(Equipment not included)

Model No. 45022

Use for Sound Level Meters

884 / 886



**Model No. 45028
for Model 260 Series**



**Model No. 45029
for Model 444**



Below is a cross-reference guide for carrying cases by model number

Model Number	Grab-N-Go	Molded Plastic	Roll-Top
160	00836		
228	00832 / 00834 / 00838	45028	
229-2	00832 / 00834 / 00838	45028	
260-6XLPM	00832 / 00834 / 00838	45028	
260-8, 8P	00832 / 00834 / 00838	45028	00248
260-8Xi, 8XPi	00832 / 00834 / 00838	45028	
260-9S, 9SP	00838	45028	
270-5	00832 / 00834 / 00838	45028	00248
372-2 / 3	00836		
444		45029	
TS112 / TS113	00832 / 00834 / 00838		
897		45021	
884-2, 886-2		45022	
8455, 8455	00836		