



SNA Terminal Blocks T&B Catalog Number:

011049117

UPC Number:

66201995413

Status:

Active

Description:

Gray, feed through miniblock with 6 mm spacing, 20 Amp rated UL current with screw clamp connection that accepts 18-12 AWG UL wire range

Features

Includes IP20 protection

Touch-safe IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Miniblock
Color	Gray
Mounting	DIN 2
Series	DR4/6.1
Connection Technology	Screw Clamp
UL Wire Range (AWG)	18-12
Rated IEC Wire Range (Solid) (mm ²)	4
Rated CSA Wire Size (AWG)	12

Dimension Information

L x W x H (mm)	28 x 31
Spacing (mm)	6
Spacing (inches)	0.238

Specifications

UL Current (Amps)	20
UL Voltage (VAC)	250
Rated UL Wire Size (AWG)	12
IEC Voltage (VAC)	500
IEC Current (Amps)	30

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	1750
T&B Sold in UOM	Each
T&B Weight Per UOM	0.02 lbs. per 100

Certifications

Approvals	IEC, UL/CSA
-----------	-------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com