

# BFMHE-10/34-3E



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → PLC Wiring Systems  
→ PLC Connecting Interfaces

## General Information

<b>Extended Product Type:</b>	BFMHE-10/34-3E
<b>Product ID:</b>	1SNA020299R0700
<b>EAN:</b>	3472590202992
<b>Catalog Description:</b>	BFMHE-10/34-3E - Connecting Interface
<b>Long Description:</b>	BFMHE Three deck single-wire interface for HE10/34 connector.

## Ordering

<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85371098

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC129120S0202
<b>Instructions and Manuals:</b>	1SNC129120S0202

## Dimensions

<b>Product Net Width:</b>	79 mm
<b>Product Net Height:</b>	75 mm
<b>Product Net Depth / Length:</b>	83 mm
<b>Product Net Weight:</b>	0.165 kg

## Technical

<b>Connection Type:</b>	Pluggable - Screw clamp
<b>Pollution Degree:</b>	2
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	7.5 mm
<b>Recommended Screw Driver:</b>	3.5 mm

## Technical UL/CSA

<b>Connecting Capacity UL/CSA:</b>	Stranded 14 AWG
<b>Flammability According to UL94:</b>	V0

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225028U1000
--	-----------------

## Classifications

**Object Classification Code:** X

**ETIM 4:** EC001604 - Fieldbus, decentr. periphery - communication module

**ETIM 5:** EC002780 - Interface module

**ETIM 6:** EC002780 - Interface module

## Container Information

**Package Level 1 Units:** 1 piece

**Package Level 1 Width:** 87 mm

**Package Level 1 Depth / Length:** 87 mm

**Package Level 1 Height:** 80 mm

**Package Level 1 Gross Weight:** 0.165 kg

**Package Level 1 EAN:** 3472590202992

**Package Level 2 Units:** 45 piece

**Package Level 2 Width:** 300 mm

**Package Level 2 Depth / Length:** 500 mm

**Package Level 2 Height:** 300 mm

**Product Packing Type:** Box



