


## Leaded Ferrite Bead Inductors (FB series A type)

## FBA04HA450AB-00



## ■ Features

- Item Summary  
45Ω, 7 A, φ 3.5x4.5mm Axial
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping 1000pcs

## ■ Products characteristics table

Impedance [100MHz]	45 Ω min
Case Size (mm)	3.5x4.5
Rated Current (max)	7 A
DC Resistance (max)	10 mΩ
Z Measuring Frequency	50 MHz
Operating Temp. Range	-25 to +85 °C (Including-self-generated heat)
Insulation Resistance (min)	1 MΩ
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Wave

## ■ External Dimensions

Dimension D	φ 3.5 ±0.2 mm
Dimension L	4.5 ±0.3 mm
Dimension d	φ 0.65 ±0.05 mm

2016.05.27

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
 Before making final selection, please check product specification.