

**Catalog Number:** CPO250-9-25  
**Product ID:** 7TAA017310R0135  
**UPC Number:** 78621087532  
**Status:** Active



Actual

Thin-Wall Heat-Shrinkable Tubing for Cable Range 16 - 10 AWG, Expanded Diameter 1/4 inch, Length 25 feet reel, rated for 600 Volt, 125 degrees C, Material: Cross-linked polyolefin - Non-lined, White

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Thin-Wall Heat-Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Voltage Rating	600V
Thickness	Thin
Length	25
Color	White

### European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	6.35mm
Inner diameter after heat-shrink	3.302mm
Nominal diameter inch	1/4 inch
Wall thickness after shrinking	0.508mm
Length	7.62m
Operation temperature	-55-+135°C
Colour	White
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

### Packaging

Inner Quantity	1
Outer Quantity	10
Outer Dimensions (inches)	13.4x13.3x6.6
Weight Uom	36.5 lbs. per 100

### Documents / Support Tools

SDS US 1	SDS-00046-TB2
Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321

