



Actual

Catalog Number: 10RC-2577
Product ID: 7TAI029690R0001
UPC Number: 78621083931
EAN Number: 05414363935735
Status: A

Nylon Fully Insulated Female Disconnect, Length 1.04 Inches, Width .38 Inches, Maximum Insulation .225, Tab Size .250x.032, Wire Range #12-#10 AWG, Color Yellow, Brass, Tin Plated

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RC2573

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Standard	UL E66716
Material	Brass
Finish	Tin Plated
Color	Yellow
Insulation	Nylon/Polyamide

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Fully Insulated
Colour insulation	Yellow
Material insulation	PA
Material	Brass

Packaging

Inner Quantity	50
Outer Quantity	250
Outer Dimensions (inches)	12.25x10.25x8
Weight Uom	7.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com