



Actual



Actual

Catalog Number: 14RB-38
Product ID: 7TAI029460R0019
UPC Number: 78621080075
EAN Number: 05414363137979
Status: A

Vinyl-Insulated Ring Terminal, Length 1.16 Inches, Width .54 Inches, Maximum Insulation .170, Bolt Hole 3/8 Inch, Wire Range #18-#14 AWG, Color Blue, Copper, Tin Plated

- These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wire's flex point.
- Brazed seam barrel is serrated to obtain high pull-out value.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RB737

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wires flex point. Brazed seam barrel is serrated to obtain high pull-out value.
Standard	UL E9809
Wire Size	18-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PVC
Colour insulation	Blue
Reel packaging	N
AWG-range	18-14
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	12.3x10.3x8.2
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website

For further technical assistance, please contact us...

ABB Installation Products Canada
 700, Thomas Avenue
 Saint-Jean-sur-Richelieu, QC
 J2X 2M9
www.tnb.ca

ABB Installation Products Technical Support
<http://www.tnb.ca/en/contactus/?id=ALL>

Hours: 7h00 - 18h00
 Monday-Friday