

Catalog Number: 2RAS18X
Product ID: 7TAI029900R0000
UPC Number: 78621070326
EAN Number: 05414363140559
Status: A



Actual

Heat Shrinkable Butt Splice, Length 1.50 Inches, Width .25 Inches, Maximum Insulation Diameter .170, Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated

- Self-insulated with heat-shrinkable polyolefin and internally coated sealant. Upon completed installation, a fully sealed connection is achieved to protect the joint against the degrading effects of galvanic action, corrosion, and environmental exposure.
- Application Tools: WT1255
- Alternate Package Qty: RAAS22X

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Sta-Kon
Type	Splice Connector
Special Features	Self-insulated with heat-shrinkable polyolefin and internally coated sealant. Upon completed installation, a fully sealed connection is achieved to protect the joint against the degrading effects of galvanic action, corrosion, and environmental exposure.
Material	Copper
Finish	Electro -Tin Plated
Color	Red
Voltage Rating	600 V
Temperature Rating	150 Degrees C

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
AWG-range	22-18
Material	Copper
Surface protection	Tinned
Insulation	Other
Colour insulation	Red
Type of connection	End connector

Packaging

Inner Quantity	50
Outer Quantity	2500
Outer Dimensions (inches)	15x9.4x8.9
Weight Uom	3.75 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com