RBB T&B-RBB

Actual

Catalog Number: 2RB14

 Product ID:
 7TAI029810R0001

 UPC Number:
 78621080020

 EAN Number:
 05414363140566

Status: A

Nylon-Insulated Butt Splice, Length 1.19 Inches, Width .21 Inches, Maximum Insulation Diameter .148, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated

- Nylon insulated splices meet or exceed the requirements of MIL-T-7928.
- These splices are color-coded according to wire size.
- Application Tools: ERG4001, WT145C, WT112M
- Alternate Package Qty: RBB21

North American Specifications (UNSPSC)		
UNSPSC	39121449 Wire or cable compression splice	
IGCC	4669 Wire or cable compression splice	
Brand Name	Sta-Kon	
Туре	Nylon Insulated Butt Splice	
Special Features	Nylon insulated splices meet or exceed the require-	
	ments of MIL-T-7928. These splices are color-cod-	
	ed according to wire size.	
Standard	UL E9809	
Material	Copper	
Finish	Electro -Tin Plated	
Color	Blue	
Voltage Rating	600 V	
Temperature Rating	105 C	

European Specifications (ETIM)		
ETIM	EC001059 Crimp splices for copper conductor	
Material	Copper	
Surface protection	Tinned	
Insulation	PA	
Colour insulation	Blue	

Packaging	
Inner Quantity	100
Inner Dimensions (inches)	12.2x10.1x8
Outer Quantity	500
Outer Dimensions (inches)	12.2x7.7x10.4
Weight Uom	3.75 lbs. per 1000

## **Documents / Support Tools**

Technical Drawing / Data Sheet US Available on Website

## For further technical assistance, please contact us...

ABB Installation Products Technical Support MS 3B-50

860 Ridge Lake Blvd. Memphis, TN 38120 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

ABB Installation Products - USA 860 Ridge Lake Blvd. Memphis, TN 38120 www.tnb.com