



Actual



Actual

Catalog Number: LTA75-100
Product ID: 7TAD012770R0005
UPC Number: 78620986528
EAN Number: 05415022244953
Status: Obsolete
Replacement Catalog: LTAES03G-C

3/4 Inch Aluminum PVC Jacketed Liquidtight Flexible Conduit

- WEEE and RoHS compliant.

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	T&B
Type	Flexible Conduit - Non-Metallic Core
Special Features	Utilizes The Flexibility of a Light-Weight Aluminum Core, Coupled with The Advantage of a PVC Jacket that is Virtually Unaffected by Sunlight, Acid and Oil.
Application	Used In Applications Where Concerns of Excessive Weight and Corrosion Exist.
Standard	RoHS
Trade Size	3/4 Inch
Length	100 Feet
Radius	3 Inch
Material	Aluminum with PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal size in inch	3/4 inch
Outer diameter	26.4mm
Inner diameter	21.1mm
Material	Aluminium
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C

Packaging

Outer Quantity	100
Outer Dimensions (inches)	20.5x7.5x20.75
Weight Uom	22 lbs. per 100

Documents / Support Tools

Technical Data Sheet Global	wsd-000277
-----------------------------	------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com