



Flexible Conduits & Fittings
T&B Catalog Number:

UPC Number: LLPA-10A.50
Status: 78620995764
Description: Active

Fine profile medium-wall very flexible black conduit. (LLPA) Material - polyamide 6, conduit size NW - 10.

Application

Machine
Renewable Energy
Technology

Characteristics

Good impact resistance also at low temperatures and dry conditions
Self-extinguishing
Free from halogens and cadmium
Good flexibility

General

Material	Polyamide 6
Material-Conduit Core	Non-Metallic
Color	Black
System	Smart Line
Compatiable With	PMA Smart Line, PMAFIX Pro, PMAFIX, PMAGRIP

Dimension Information

Conduit Size (inches)	5/16
Conduit Size NW (mm)	10
Conduit Size Metric (mm)	12
Inside Diameter (inches)	0.38
Outside Diameter (inches)	0.51
Inside Diameter (mm)	9.6
Outside Diameter (mm)	13
Static Radius (mm)	20
Rec. Fitting Thread-Metric	M12 x 1.5
Rec. Fitting Thread-PG	9

Technical Information

Temperature Range-Continuous (Celsius)	-40 to +105
Temperature-Short-Term (Celsius)	140
Fatigue Life	High
Technical Data Sheet	Available on Website
Chemical Resistance Chart	Available on Website

Packaging

T&B Inner Pack	1
Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	3.3 lbs. Each

Application Support

PMA Reference Guide	Available on Website
Conduit Guide-Smart Line	Available on Website
Product Overview-Smart Line Conduits	Available on Website
Product Overview-Smart Line Connectors	Available on Website
Product Overview-System Supports	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com