



Representative

Catalog Number: A482
Product ID: 7TAI029620R0005
UPC Number: 78621080867
Status: A

Non-Insulated Rectangular Ring Terminal, Length .96 Inches, Width .302 Inches, Bolt Hole #8, Wire Range #22-#18 AWG, Copper, Tin Plated

- Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
- Application Tools: ERG4002

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Non-Insulated Rectangular Ring Terminal
Special Features	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standard	UL E9809
Wire Size	22-18 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	22-18
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	3x4x4
Outer Quantity	10000
Outer Dimensions (inches)	21.5x9x3.9
Weight Uom	2.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com