



Representative

Catalog Number: B71
Product ID: 7TAI029620R0026
UPC Number: 78621080924
EAN Number: 05414363935063
Status: A

Non-Insulated Ring Terminal, Length .93 Inches, Width .50 Inches, Bolt Hole 1/4 Inch, Wire Range #18-#14 AWG, Copper, Tin Plated, 1,000 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002
- Alternate Package Qty: B14-14

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Non-Insulated Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	18-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	18-14
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	4x4x3
Outer Quantity	10000
Outer Dimensions (inches)	16x9.6x6.9
Weight Uom	2.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.

ABB Installation Products Technical Support
MS 3B-50

Hours: 7AM - 6PM CDT
Monday-Friday

Memphis, TN 38120
www.tnb.com

860 Ridge Lake Blvd.
Memphis, TN 38120

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com