



Representative

**Catalog Number:** B86  
**Product ID:** 7TAI029620R0029  
**UPC Number:** 78621080936  
**EAN Number:** 05414363148586  
**Status:** A

Non-Insulated Ring Terminal, Length .75 Inches, Width .31 Inches, Bolt Hole #8, Wire Range #18-#14 AWG, Copper, Tin Plated, 1,000 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002
- Alternate Package Qty: B14-8

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	18-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

### European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	18-14
Material	Copper
Surface protection	Tinned

### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	10000
Outer Dimensions (inches)	16.3x6.8x4.2
Weight Uom	1.88 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**For further technical assistance, please contact us...**

Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

860 Ridge Lake Blvd.  
Memphis, TN 38120

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)