



Representative

**Catalog Number:** C10-8-SK  
**Product ID:** 7TAI029580R0020  
**UPC Number:** 78621080343  
**EAN Number:** 05414363148968  
**Status:** A

Non-Insulated Ring Terminal, Length .82 Inches, Width .31 Inches, Bolt Hole #8, Wire Range #12-#10 AWG, Copper, Tin Plated

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002
- Alternate Package Qty: C77

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Non-Insulated Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	12-10 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

### European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	2.63x1.63x3.5
Outer Quantity	250
Outer Dimensions (inches)	10.4x8.7x7.2
Weight Uom	4.38 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**For further technical assistance, please contact us...**

Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

860 Ridge Lake Blvd.  
Memphis, TN 38120

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)