



Representative

**Catalog Number:** C480  
**Product ID:** 7TAI029620R0045  
**UPC Number:** 78621081124  
**Status:** Active

Non-Insulated Rectangular Ring Terminal, Length 1.27 Inches, Width .390 Inches, Bolt Hole #8, Wire Range #12-#10 AWG, Copper, Tin Plated

- Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
- Application Tools: ERG4002

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Rectangular Ring Terminal
Special Features	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standard	UL E9809
Wire Size	12-10
Voltage Rating	600V
Material	Copper
Color	Metallic

### European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

### Packaging

Inner Quantity	500
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	5000
Outer Dimensions (inches)	4.3x24.1x11.2
Weight Uom	6.25 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)