



Representative

Catalog Number: C70
Product ID: 7TAI029630R0073
UPC Number: 78621081078
Status: A

Non-Insulated Ring Terminal, Length .98 Inches, Width .50 Inches, Bolt Hole 5/16 Inch, Wire Range #12-#10 AWG, Copper, Tin Plated, 500 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002
- Alternate Package Qty: C10-516

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Non-Insulated Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	12-10 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	500
Inner Dimensions (inches)	4x4x3
Outer Quantity	5000
Outer Dimensions (inches)	16x9.6x6.8
Weight Uom	4.38 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com