



Representative

Catalog Number: C73
Product ID: 7TAI029630R0075
UPC Number: 78621081084
EAN Number: 05414363149170
Status: A

Non-Insulated Ring Terminal, Length 1.10 Inches, Width .59 Inches, Bolt Hole 3/8 Inch, Wire Range #12-#10 AWG, Copper, Tin Plated, 500 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002
- Alternate Package Qty: C10-38

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Non-Insulated Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	12-10 AWG
Voltage Rating	600 V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	500
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	5000
Outer Dimensions (inches)	16.25x9.75x6.75
Weight Uom	5.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

For further technical assistance, please contact us...

Memphis, TN 38120
www.tnb.com

860 Ridge Lake Blvd.
Memphis, TN 38120

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com