



Actual

Catalog Number: F2022
Product ID: 7TAI029790R0001
UPC Number: 78621033987
EAN Number: 05414363151067
Status: Active

Polypropylene-Insulated Ferrule, Total Length .610 Inches/15.5mm, Pin Length .394 Inches/10mm, Pin Diameter .043 Inches/1.1mm, Base Diameter .098 Inches/2.5mm, Wire Range 20 AWG/.5mm², Color White, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: T1, T3, ERG4

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ferrule
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
Standard	UL E489056
Wire Size	20
Material	Copper
Color	White

European Specifications (ETIM)

ETIM	EC000005 Cable end sleeve
Construction type	Standard
Nominal cross section	0.5mm ²
Insulated	Y
Insulation material	Polypropylene
Colour	White
Material	Copper
Surface protection	Tinned
With identification flag	N
Reel packaging	N

Packaging

Inner Quantity	500
Outer Quantity	5000
Weight Uom	0.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com