



Actual

**Catalog Number:** F2036  
**Product ID:** 7TAI029780R0008  
**UPC Number:** 78621033516  
**EAN Number:** 05414363151128  
**Status:** A

Polypropylene-Insulated Ferrule, Total Length .748 Inches/19mm, Pin Length .472 Inches/12mm, Pin Diameter .091 Inches/2.3mm, Base Diameter .165 Inches/4.2mm, Wire Range 14 AWG/2.50mm<sup>2</sup>, Color Blue, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: FER9500, FER9501, ERG4

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Polypropylene Insulated Ferrule
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
Standard	UL E489056
Wire Size	14 AWG
Material	Copper
Color	Blue

### European Specifications (ETIM)

ETIM	EC000005 Cable end sleeve
Construction type	Standard
Nominal cross section	2.5mm <sup>2</sup>
Insulated	Y
Insulation material	Polypropylene
Colour	Blue
Material	Copper
Surface protection	Tinned
With identification flag	N
Reel packaging	N

### Packaging

Inner Quantity	500
Outer Quantity	5000
Outer Dimensions (inches)	8.1x6x3.8
Weight Uom	0.63 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
 www.tnb.com

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com