



Actual

Catalog Number: F2046
Product ID: 7TAI029790R0018
UPC Number: 78621033550
EAN Number: 05415022180671
Status: A

Polypropylene-Insulated Ferrule, Total Length 1.142 Inches/29mm, Pin Length .708 Inches/18mm, Pin Diameter .236 Inches/6mm, Base Diameter .346 Inches/8.8mm, Wire Range 6 AWG/16.00mm², Color Blue, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: FER9500, FER9501, ERG4

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Polypropylene Insulated Ferrule
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
Standard	UL E489056
Wire Size	6 AWG
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC000005 Cable end sleeve
Construction type	Standard
Nominal cross section	6mm ²
Insulated	Y
Insulation material	Polypropylene
Colour	Blue
Material	Copper
Surface protection	Tinned
With identification flag	N
Reel packaging	N

Packaging

Inner Quantity	100
Outer Quantity	1000
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com