



Actual

Catalog Number: F8009
Product ID: 7TAI029790R0047
UPC Number: 78621033570
EAN Number: 05415022255386
Status: A

Polypropylene Insulated Twin Ferrule, Length .787 Inch/18.5mm, Pin Length .394 Inch/10mm, Pin Diameter .114 Inch/2.9mm, Base Diameter .295 Inch/7.5mm, Conductor Range 2x14 AWG/2x2.50mm², Color Blue, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: T3

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ferrule
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
Standard	UL E489056
Wire Size	2x14 AWG
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC000005 Cable end sleeve
Construction type	Twin cable end sleeve
Nominal cross section	2.5mm ²
Insulated	Y
Insulation material	Polypropylene
Colour	Blue
Material	Copper
Surface protection	Tinned
With identification flag	N
Reel packaging	N

Packaging

Inner Quantity	500
Outer Quantity	5000
Weight Uom	0.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com