



Actual

Catalog Number: L-8-18-0-M
Product ID: 7TAG054070R0010
UPC Number: 72849491770
EAN Number: 05414363128588
Status: A

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 203mm (7.99 Inches), Width of 2.5mm (0.10 Inch), Thickness of 1.2mm (0.05 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

- Application Tools: ERG50, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Miniature
Standard	UL E49405
Width	0.1 in ; 2.54 mm
Length	7.99 in ; 203 mm
Thickness	0.05 in ; 1.2 mm
Bundle Diameter	0.0625 to 2 in ; 1.59 to 50.8 mm
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	18 pounds ; 80 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.5mm
Length belt/tape/tie	203mm
Tie thickness	1.2mm
Min. holding force	80N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12x9x2.75
Outer Quantity	20000
Outer Dimensions (inches)	17.4x12.8x13.8
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000218
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com