



Actual

Catalog Number: L-8-18-9-M
Product ID: 7TAG054060R0027
UPC Number: 72849491790
EAN Number: 05414363128595
Status: A

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 203mm (7.99 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

- Application Tools: ERG50, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Minature
Standard	UL E49405
Width	0.1 in ; 2.54 mm
Length	7.99 in ; 203 mm
Thickness	0.05 in ; 1.2 mm
Bundle Diameter	0.0625 to 2 in ; 1.59 to 50.8 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	18 pounds ; 80 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.5mm
Length belt/tape/tie	203mm
Tie thickness	1.2mm
Min. holding force	80N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12x9x2.75
Outer Quantity	20000
Outer Dimensions (inches)	17.4x12.9x13.8
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000218
--------------------------------	------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com