



Actual

**Catalog Number:** MCC50M8  
**Product ID:** 7TAH007940R0052  
**UPC Number:** 78621095770  
**EAN Number:** 05415022157802  
**Status:** A

Copper One-Hole Metric Lug, Standard Barrel, Peep Hole, Max 35kV, 50mm<sup>2</sup> Wire Size, 8mm Bolt Size, Tin Plated

- Manufactured from seamless copper tubing that conforms to BS2781 with heavy-duty wall thickness, achieving maximum conductivity with low resistance.
- Electro Tin-Plated for Corrosion Resistance. Chamfered Barrels Provide Ease of Strand Entry and Inspection hole facilitates full insertion of the conductor.
- Cable Area Clearly Identified on Lug.
- #N/A

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel
Standard	UL E9809
Cable Size	50 mm <sup>2</sup>
Stud Size	M8
Number Of Holes	1
Voltage Rating	35 kV
Insulation	None
Material	Copper

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	4x4x3
Outer Quantity	500
Outer Dimensions (inches)	21.5x9x4
Weight Uom	4.75 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000151
Instruction Sheet	TA02990-TB2

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)