




Color-Keyed® PRINT

Standard Barrel Copper Lug

T&B Catalog Number: 54108
UPC Number: 78621054108
Status: Active

Description:

Copper One-Hole Lug - Straight Standard Barrel - max 35KV, #1 AWG Wire, 1/4" Bolt Size, Tin Plated with Inspection Hole, Green 37



ROHS INSTALL SUBMITTAL PACKAGE

Where To Buy

Enter Zip Code:

Enter Quantity:

General

Material	Copper
Finish	Tin Plated
Wire Size	#1 AWG
Number of Studs	1
Stud Size	1/4
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Green
Die Code	37

Dimension Information

A (inches)	1.50
B (inches)	0.65
C (inches)	0.68
D (inches)	0.11
E (inches)	0.47
F (inches)	1/4

Tooling

Connector & Tooling Chart [Click Here](#)

Packaging

Inner Package	20
Outer Package	200
Package Height	4
Package Length	12.4
Package Width	6.3
T&B Sold in UOM	Each
T&B Weight Per UOM	1.69 lbs. per 100

Application Support

T&B Instruction Sheets [ta00675-tb2](#)
 Product Overview [Click Here](#)

Notes

- Dimensions given for reference only. Dimensions may vary up to .030.

Certifications

RoHS Compliance [Yes](#) [Generate Compliance Certificate](#)

HOME

[Global Site](#)
[Report Issue](#)

LOGIN

[T&B Access \(Dist only\)](#)
[Suppliers](#)
[MyTNB](#)

RESOURCES

[Catalog PDFs](#)
[End User Toolkit](#)
[Solution Set Brochures](#)
[Vertical Market Brochures](#)
[Where To Buy](#)

SUPPORT

[Contact Us](#)
[Global Locations](#)
[Product Support](#)
[Tool Services](#)
[Legal/Privacy](#)

COMPANY

[About Us](#)
[Careers](#)
[Employees](#)
[News](#)

