



PRINT

Ring Terminal

T&B Catalog Number: K971
UPC Number: 78621081577
Status: Active

Description:

Non-Insulated Tubular Ring Terminal, Length 2.08 Inches, Width .93 Inches, Bolt Hole 1/4 Inch, Wire Range 2/0AN-3/0, Copper, Tin Plated, 50 Pack



ROHS SUBMITTAL PACKAGE

Where To Buy

Enter Zip Code:

Enter Quantity:

Features

- These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indentor or double indentor (recommended for solid wire).

General

Insulation Type	Non-Insulated - Tubular
Terminal Series	K
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	2/0AN-3/0
Stud Size	1/4

Dimension Information

Stock Thickness	.06
A (inches)	2.08
B (inches)	.93
C (inches)	.54
M (inches)	1.69

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0
ML Specification	MS-20659-153

Tooling

Tool Charts	Click Here
Application Tools	TBM6, TBM6S, WT3185
Recommended Tool	TBM6S

Packaging

Order Multiple	50
Inner Package	50
Outer Package	250
Package Type	Standard
Package Height	4.2
Package Length	24
Package Width	5.5
T&B Sold in UOM	Each
T&B Weight Per UOM	7.69 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000219
Overview	Click Here
Wire Guide Tables	Click Here

Notes

- Not available on Mylar Tape.

Certifications

RoHS Compliance [Yes](#) [Generate Compliance Certificate](#)

Certifications



File Nbr:
E9809