



PRINT

**Intermediate**

**T&B Catalog Number:** L-8-40-0-M  
**UPC Number:** 72849491830  
**Status:** Active

**Description:**

Intermediate Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 215mm (8.46 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack

ROHS SUBMITTAL PACKAGE

**Where To Buy**

Enter Zip Code:

Enter Quantity:

**General**

**Material:** Nylon 6.6 Weather Resistant  
**Color:** Black

**Dimension Information**

**Nominal Length (inches):** 8  
**Length (inches):** 8.5  
**Width (inches):** 0.130  
**Max. Wire Bundle Diameter (inches):** 2  
**Min. Wire Bundle Diameter (inches):** 1/16

**Specifications**

**Temperature Rating:** -40°F to 185°F  
**Flammability Rating:** UL 94 V-2

**Tooling**

**Application Tools:** [ERG50, QC-100, L-200, L-400-C](#)

**Packaging**

**Order Multiple:** 1000  
**Inner Package:** 1000  
**Outer Package:** 10000  
**Package Type:** Bulk  
**Package Height:** 10.6  
**Package Length:** 17.1  
**Package Width:** 13.2  
**T&B Sold in UOM:** Each  
**T&B Weight Per UOM:** 1.88 lbs. per 1000

**Application Support**

T&B Sales Drawings: [wsd-000221](#)  
 Overview: [Click Here](#)  
 Material Selection Guide: [Click Here](#)  
 Available Colors: [Click Here](#)

**Certifications**

**RoHS Compliance:** Yes [Generate Compliance Certificate](#)

**Certifications**



**HOME**

[Global Site](#)  
[Report Issue](#)

**LOGIN**

[T&B Access \(Dist only\)](#)  
[Suppliers](#)  
[MyTNB](#)

**RESOURCES**

[Catalog PDFs](#)  
[End User Toolkit](#)  
[Solution Set Brochures](#)  
[Vertical Market Brochures](#)  
[Where To Buy](#)

**SUPPORT**

[Contact Us](#)  
[Global Locations](#)  
[Product Support](#)  
[Tool Services](#)  
[Legal/Privacy](#)

**COMPANY**

[About Us](#)  
[Careers](#)  
[Employees](#)  
[News](#)

