



Actual

**Catalog Number:** RA2257  
**Product ID:** 7TAI029500R0003  
**UPC Number:** 78621081792  
**Status:** A

Vinyl-Insulated Locking Fork Terminal, Length .97 Inches, Width .29 Inches, Maximum Insulation .150, Bolt Hole #10, Wire Range #22-#16 AWG, Color Red, Copper, Tin Plated, 1,000 Piece

- Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.
- Application Tools: ERG4001, WT145C, WT2000, WT112M, WT145C
- Alternate Package Qty: 18RA-10FL

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Vinyl Insulated Locking Fork Terminal
Special Features	Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.
Standard	UL E9809
Wire Size	22-16 AWG
Voltage Rating	600 V
Material	Copper
Color	Red

### European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Fork shape
Insulation	PVC
Colour insulation	Red
Reel packaging	N
AWG-range	22-16
Material	Copper
Surface protection	Tinned

### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	5000
Outer Dimensions (inches)	10.4x8.7x7.1
Weight Uom	1.88 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)