



Actual

Catalog Number: RA2577F
Product ID: 7TAI029740R0013
UPC Number: 78621089443
EAN Number: 05414363157731
Status: Active

Nylon Insulated Open Top 90 Degree Flag Female Disconnect Terminal, Length .80 Inch, Width .71 Inch, Maximum Insulation .170, Tab Size .250x.032, Wire Range #22-#18 AWG, Color Red, Brass, Tin Plated, 500 Pack

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RA18250A

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Standard	UL E66716
Material	Brass
Finish	Tin Plated
Color	Red
Insulation	Nylon/Polyamide

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Red
Material insulation	PA
Material	Brass

Packaging

Inner Quantity	500
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	5000
Outer Dimensions (inches)	17x10x7.7
Weight Uom	3.75 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com