



Representative

Catalog Number: RB1153
Product ID: 7TAI029860R0022
UPC Number: 78621081909
EAN Number: 05414363933984
Status: A
Replacement Catalog: RB14-10F

Nylon Insulated Fork Terminal, Length .87 Inches, Width .38 Inches, Maximum Insulation .162, Bolt Hole #10, Wire Range #18-#14 AWG, Color Blue, Copper, Tin Plated

- Inner bronze insulation grip sleeve lengthens flex radius of conductor and eliminates conductor creep.
- Nylon jacket is color-coded.
- Application Tools: WT145C, WT2000, WT112M, ERG4001, WT145A
- Alternate Package Qty: RB14-10F

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Nylon Insulated Fork Terminal
Special Features	Inner bronze insulation grip sleeve lengthens flex radius of conductor and eliminates conductor creep. Nylon jacket is color-coded.
Standard	UL E9809
Wire Size	18-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Fork shape
Insulation	PA
Colour insulation	Blue
Reel packaging	N
AWG-range	18-14
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	10000
Outer Dimensions (inches)	16.2x9.6x6.9
Weight Uom	2.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com