



Actual

Catalog Number: RB481
Product ID: 7TAI029870R0039
UPC Number: 78621081826
Status: A

Nylon Insulated Rectangular Ring Terminal, Length 1.109 Inches, Width .302 Inches, Bolt Hole #6, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated

- Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
- Application Tools: ERG4001, WT145C

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Rectangular Ring Terminal
Special Features	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standard	UL E9809
Wire Size	16-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Blue
Reel packaging	N
AWG-range	16-14
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	10000
Outer Dimensions (inches)	17x10x7.7
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000316
--------------------------------	------------

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com