



Actual

Catalog Number: RBB21
Product ID: 7TAI029850R0018
UPC Number: 78621081951
EAN Number: 05414363158851
Status: A

Nylon Insulated Butt Splice, Length 1.19 Inches, Width .21 Inches, Maximum Insulation Diameter .148, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated, 1,000 Pack

- Nylon insulated splices meet or exceed the requirements of MIL-T-7928.
- These splices are color-coded according to wire size.
- Application Tools: ERG4001, WT145C, WT112M
- Alternate Package Qty: 2RB14

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Sta-Kon
Type	Splice Connector
Special Features	Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size.
Standard	UL E9809
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Voltage Rating	600 V
Temperature Rating	105 Degrees C

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Material	Copper
Surface protection	Tinned
Insulation	PA
Colour insulation	Blue

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	10000
Outer Dimensions (inches)	17x10.2x6.8
Weight Uom	3.75 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com