



Actual

Catalog Number: RC10-250F
Product ID: 7TAI029690R0015
UPC Number: 78621087420
EAN Number: 05414363131977
Status: A

Nylon Insulated Female Disconnect, Length 1.04 Inches, Width .29 Inches, Maximum Insulation .215, Tab Size .250x.032, Wire Range #12-#10, Color Yellow, Copper, Tin Plated, 50 Pack

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RC250

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Type	Nylon Insulated Female Disconnect
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Standard	UL E66716
Material	Brass
Finish	Tin Plated
Color	Yellow
Insulation	Nylon/Polyamide

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Yellow
Material insulation	PA
Material	Copper

Packaging

Inner Quantity	50
Inner Dimensions (inches)	2.09x1.1x3
Outer Quantity	250
Outer Dimensions (inches)	10.25x9x7.2
Weight Uom	5.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com