



Actual

Catalog Number: RC1253
Product ID: 7TAI029860R0047
UPC Number: 78621082037
EAN Number: 05414363159209
Status: Active

Nylon Insulated Fork Terminal with Flanged Tongue, Length 1.00 Inches, Width .38 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, 500 Pack

- Fork terminals allow easy installation because screw needs only to be loosened.
- A flanged-tongue fork with turned up tips provide fo extra holding protection.
- Application Tools: WT145C, WT2000, WT112M, ERG4001, WT145A
- Alternate Package Qty: RC1010FS

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Fork Terminal Flanged Tongue
Special Features	Fork terminals allow easy installation because screw needs only to be loosened. A flanged-tongue fork with turned up tips provide fo extra holding protection.
Standard	UL E9809
Wire Size	12-10
Voltage Rating	600V
Material	Copper
Color	Yellow

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Fork shape
Insulation	PA
Colour insulation	Yellow
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	500
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	5000
Outer Dimensions (inches)	15.9x9.8x6.8
Weight Uom	1 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

