



Actual

Project: Joaaquin

Catalog Number: RC2213
Product ID: 7TAI029860R0050
UPC Number: 78621088764
EAN Number: 05414363933465
Status: A

Nylon Insulated Locking Fork Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #8, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, 500 Pack

- Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.
- Application Tools: ERG4001, WT145C, WT2000, WT112M, WT145A
- Alternate Package Qty: RC10-8FL

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Nylon Insulated Locking Fork Terminal
Special Features	Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.
Standard	UL E9809
Wire Size	12-10 AWG
Voltage Rating	600 V
Material	Copper
Color	Yellow

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Fork shape
Insulation	PA
Colour insulation	Yellow
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	500
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	5000
Outer Dimensions (inches)	17x10x7
Weight Uom	5.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US [Available on Website](#)

For further technical assistance, please contact us...

Memphis, TN 38120
www.tnb.com

860 Ridge Lake Blvd.
Memphis, TN 38120

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com