



Representative

Catalog Number: RC484
Product ID: 7TAI029860R0058
UPC Number: 78621081995
EAN Number: 05414363933359
Status: A

Nylon Insulated Rectangular Ring Terminal, Length 1.203 Inches, Width .237 Inches, Bolt Hole #6, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated

- Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
- Application Tools: ERG4002

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Nylon Insulated Rectangular Ring Terminal
Special Features	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standard	UL E9809
Wire Size	12-10 AWG
Voltage Rating	600 V
Material	Copper
Color	Yellow

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Yellow
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	500
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	5000
Outer Dimensions (inches)	17x10x7.7
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000316
Catalog Page	Available on Website

For further technical assistance, please contact us...

ABB Installation Products Canada
 700, Thomas Avenue
 Saint-Jean-sur-Richelieu, QC
 J2X 2M9
www.tnb.ca

ABB Installation Products Technical Support
<http://www.tnb.ca/en/contactus/?id=ALL>

Hours: 7h00 - 18h00
 Monday-Friday