



Actual

**Catalog Number:** TC817-TB  
**Product ID:** 7TAG009840R0020  
**UPC Number:** 78621082631  
**EAN Number:** 05414363059240  
**Status:** A

Low-Profile Mounting Plate, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 11.1mm (0.437 Inches), Width of 11.1mm (0.437 Inches), Height of 4.75mm (0.187 Inches), Epoxy Glue Mounting Method

- These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	Mounting Base
Special Features	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Epoxy Glue (TC2PA)
Operating Temperature	-40 to +185 F

### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	11.1mm
Width	11.1mm
Height	4.75mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12.5x6.8x9.6
Outer Quantity	10000
Outer Dimensions (inches)	12.1x9.1x6.3
Weight Uom	1.08 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)