



Actual

Catalog Number: TV14-10BL-XV
Product ID: 7TAI029350R0243
UPC Number: 72849414461
EAN Number: 05414363489245
Status: A

Insulated Vinyl Blade Terminal, Wire Range 16-14 AWG, Blue, Canister, Reusable Packaging

- For use in DIN-Style Blade Terminal blocks. Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations.
- Application Tools: WT112M, CM2000A
- Alternate Package Qty: TV1410BLL

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Catamount
Type	Blade Terminal
Special Features	For use in DIN-Style Blade Terminal blocks. Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations.
Standard	UL E9809
Wire Size	16-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Insulation	PVC
AWG-range	16-14

Packaging

Inner Quantity	75
Inner Dimensions (inches)	6x4.5x4
Outer Quantity	900
Outer Dimensions (inches)	10.7x10x7.9
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US [Available on Website](#)

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com