



Actual

**Catalog Number:** TY525M  
**Product ID:** 7TAG009170R0000  
**UPC Number:** 78621080509  
**EAN Number:** 05414363065616  
**Status:** A

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 185.67mm (7.31 Inches), Width of 4.67mm (0.184 Inches), Thickness of 1.09mm (0.043 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.
- Application Tools: ERG50, WT1-TB

#### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standard	UL E49405
Width	0.184 in ; 4.67 mm
Length	7.31 in ; 185.67 mm
Thickness	0.043 in ; 1.09 mm
Bundle Diameter	0.138 to 1.77 in ; 3.5 to 45 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 222 newtons

#### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.67mm
Length belt/tape/tie	185.67mm
Tie thickness	1.09mm
Min. holding force	222N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N



Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	10.5x5x0
Outer Quantity	1000
Outer Dimensions (inches)	9.7x6.7x7.9
Weight Uom	5 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

#### For further technical assistance, please contact us...

ABB Installation Products - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
www.tnb.com

ABB Installation Products Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com