



Actual

Catalog Number: TYZ523M
Product ID: 7TAG009620R0006
UPC Number: 78621077043
EAN Number: 05414363068167
Status: A

High Performance Cable Tie, Aquamarine Fluoropolymer ETFE for Temperatures up to 150 Degrees Celsius (302 F), Length of 91mm (3.6 Inches), Width of 2.5mm (0.1 Inch), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), 100 Pack

- Application Tool: ERG50/1-3

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Ty-Rap
Type	Radiation Resistant
Standard	UL E49405, CSA 2884
Width	0.1 in ; 2.5 mm
Length	3.6 in ; 91 mm
Thickness	0.04 in ; 1 mm
Bundle Diameter	0.1 to 0.62 in ; 2.5 to 15.8 mm
Material	Fluoropolymer ETFE
Color	Aquamarine
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds ; 80 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.5mm
Length belt/tape/tie	91mm
Tie thickness	1mm
Max. bundle diameter	15.8mm
Min. holding force	80N
Operating temperature	-45-+150°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Other
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	N
Colour	Other
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	100
Inner Dimensions (inches)	7x3.5x0
Outer Quantity	500
Outer Dimensions (inches)	12.8x10.5x10.7
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

Technical Drawing / Data Sheet Canada Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com