



Envi-Ro-Tech™ 1676 Defluxer - DISCONTINUED

General Purpose Defluxer 1676

Introduction

This general duty azeotropic defluxer for R, RA, RMA and SA type fluxes. Can be used as an all-purpose cleaner to remove light oils, silicones, waxes, greases and similar contaminants often found in electronics manufacturing.

Features / Benefits

- Non-Flammable
- Rapidly Evaporating
- Zero Residue
- Non-Corrosive

Physical Properties

Boiling Point	30°C / 86°F
Flash Point (TCC)	None
Evaporation Rate	>1
Surface Tension	
Kauri-Butanol (KB Value)	

Chemical Components

Dichlorofluoroethane..... (1717-00-6)	90-95%-Aerosol 98-100%-Bulk
Methanol.....(67-56-1)	4-4.5%-Aerosol 3.8%-Bulk
Ethyl-S(-)-2-hydroxypropionate.....(97-64-3)	<1%-Aerosol 1-2%-Bulk
Carbon Dioxide (Aerosol Propellant)..... (124-38-9)	<3%

Plastic Compatibility

Material	Compatibility	Material	Compatibility
ABS	Not Compatible	PMMA	Not Compatible
Nylon	Excellent	POM	Excellent
Lexan	Not Compatible	PP	Excellent
HDPE	Excellent	PS	Not Compatible
CDPE	Excellent	PTFE	Excellent
C. E. Phenolic	Excellent	PVC	Excellent

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

Envi-Ro-Tech™ 1676 Defluxer is available in the following sizes:

1676-22S	22 Ounce Aerosol
1676-G	1 Gallon in Glass
1676-5G	50 Pounds in Metal
1676-54G	500 Pounds in Metal

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America
Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe
Techspray International
UNIT 4, 44/46 Bunyan Road, Kempston
Bedford MK42 8HL United Kingdom
+44 (0) 1234 855443
email: tseurope@techspray.com

Countries Outside US
Call to locate a distributor
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Techspray
P.O. Box 949
Amarillo, TX 79105
www.techspray.com



Copyright 2006 Techspray
For Commercial Use Only