



brushes

- Home
- Products »
- 141b Solutions »
- Find a Distributor
- MSDS
- Request Sample
- Company Info »

- General Cleaning Brushes
- Technical Cleaning Brushes
- Static Sensitive Brushes
- Instrument Cleaning Brushes
- Static Dissipative Brushes

General Cleaning Brushes



2020-1
7 3/4" wooden handle with 7/16" horse hair bristles.



2022-1
8 3/8" wooden handle with 3/4" hog hair bristles.



2025-1
7 3/4" wooden handle with 7/16" brass .003" bristles.



2027-1
5" wooden handle with 1/2" hog hair bristles.



2029-1
5" wooden handle with 1/2" horse hair bristles.



2021-1
7 3/4" wooden handle with 7/16" hog hair bristles.



2023-1
7 3/16" polypropylene handle with 1" horse hair bristles.



2026-1
10 3/16" wooden handle with 3/4" horse hair bristles.



2028-1
7 3/4" wooden handle with 7/16" stainless steel .006" bristles.

Technical Cleaning Brushes



2030-1
3 1/2" stainless steel handle with 1/8" goat hair bristles



2032-1
4 1/2" CAD plated steel handle with 1/4" & 3/16" horse hair bristles



2031-1
4 1/2" stainless steel handle with 1/2" & 1/4" horse hair bristles



2033-1
4 1/2" CAD plated steel handle with 3/4" horse hair bristles

Static Sensitive Brushes



2040-1
6 7/16" aluminum handle with 7/16" horse hair bristles



2042-1
6 7/16" aluminum handle with 7/16" horse hair bristles



2047-1
3 1/2" stainless steel handle with 1/8" .003" stainless steel bristles



2041-1
6 7/16" aluminum handle with 7/16" .003 stainless steel bristles



2043-1
6 7/16" aluminum handle with 7/16" .003 stainless steel bristles

Instrument Cleaning Brushes



2051-1
6" Delrin handle with 3/16" stainless steel .003" bristles.

Static Dissipative Brushes



2060-1
6 7/16" aluminum handle with 7/16" proprietary static dissipative nylon bristles



2062-1
4 1/2" zinc plated steel handle with 1/4" & 3/16" proprietary static dissipative nylon bristles



2064-1
3 1/2" Stainless steel handle with 1/8" proprietary static dissipative nylon bristles



2061-1
6 7/16" aluminum handle with 7/16" proprietary static dissipative nylon bristles



2063-1
4 1/2" zinc plated steel handle with 1/2" & 1/4" proprietary static dissipative nylon bristles