



Product Information

# C/D Solv™ Natural

## Natural Based Cleaner/Degreaser

### 3030

Introduction

---

C/D-Solv™ Natural is a natural based, low odor terpene. This aggressive solvent easily removes grease, oil, adhesives, tar, wax and similar contaminants with no rinsing required. The non-ozone depleting formula does not contain CFCs, 1,1,1-trichloroethane, or other chlorinated solvents.

Features / Benefits

- Natural Solvent
- Very Low Odor
- Non-Ozone Depleting
- Controlled Evaporation
- Safe on Most Plastics
- Rapidly Penetrating
- Residue Free
- Non-Corrosive

Physical Properties	
<b>Boiling Point</b>	53°C / 127.4°F
<b>Flash Point (TCC)</b>	149°C / 300°F
<b>Evaporation Rate</b>	NIF
<b>Surface Tension</b>	24
<b>Kauri-Butanol (KB Value)</b>	40

Chemical Components

---

Aliphatic Hydrocarbon.....	(64742-47-8)	50-60%
Carbon Dioxide (Aerosol Propellant).....	(124-38-9)	1-5%

Plastic Compatibility

---

Material	Compatibility	Material	Compatibility
<b>ABS</b>	Excellent	<b>PMMA</b>	Not Compatible
<b>Nylon 6</b>	Excellent	<b>POM</b>	Excellent
<b>Lexan</b>	Not Compatible	<b>PP</b>	Excellent
<b>HDPE</b>	Excellent	<b>PS</b>	Not Compatible
<b>LDPE</b>	Excellent	<b>PTFE</b>	Excellent
<b>Phenolic</b>	Excellent	<b>PVC</b>	Excellent

Environmental Policy

---

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

## Packaging and Availability

---

C/D Solv™ Natural is available in the following sizes:

3030-15S	15 Ounce Aerosol
3030-5G	33 Pounds in Metal

## Resources

---

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

North America  
Tech Spray L.P.  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
email: [tsales@techspray.com](mailto:tsales@techspray.com)

Europe  
Techspray International  
UNIT 4, 44/46 Bunyan Road, Kempston  
Bedford MK42 8HL United Kingdom  
+44 (0) 1234 855443  
email: [tseurope@techspray.com](mailto:tseurope@techspray.com)

Countries Outside US  
Call to locate a distributor  
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.  
P.O. Box 949  
Amarillo, TX 79105  
[www.techspray.com](http://www.techspray.com)

Aerosol MSDS  
[English](#)  
[French](#)  
[German](#)  
[Italian](#)  
[Spanish](#)

Bulk MSDS  
[English](#)  
[French](#)  
[German](#)  
[Italian](#)  
[Spanish](#)

