



Advanex™ 10

All Purpose Lubricant
3100

Introduction

Advanex™ 10 is a general purpose, economy lubricant for all industrial applications. This high flash point lubricant, combined with a non-flammable propellant, makes Advanex™ 10 the ideal choice. Advanex™ 10 penetrates quickly, leaving a thin, protective coating that cleans and lubricates delicate parts and mechanisms. It does not contain CFCs, 1,1,1-trichloroethane or other ozone depleting solvents.

Features / Benefits

- Cleans and Protects
- Economy Lubricant
- Flash Point Above 140°F
- Loosens Corrosion
- Penetrates Rapidly
- Safe on Plastics & Metals
- Non-Ozone Depleting

Chemical Components

Aliphatic hydrocarbon.....	(64742-47-8)	80-90%
Dipropylene glycol monomethyl ether.....	(34590-94-8)	1-5%
Oxygenated hydrocarbon		1-5%
Naphthenic Oil.....	(64742-46-7)	10-15%
Carbon Dioxide (Aerosol Propellant).....	(124-38-9)	1-5%

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

Advanex™ 10 is available in the following sizes:

- 3100-15S 15 Ounce Aerosol

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America
Tech Spray L.P.
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe
Techspray International
UNIT 4, 44/46 Bunyan Road, Kempston
Bedford MK42 8HL United Kingdom
+44 (0) 1234 855443
email: tseurope@techspray.com

Countries Outside US
Call to locate a distributor
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.
P.O. Box 949
Amarillo, TX 79105
www.techspray.com

[English MSDS](#)
[French MSDS](#)
[German MSDS](#)
[Italian MSDS](#)
[Spanish MSDS](#)

