



## MRS-34-30 Product Details

[Share](#) | [Print](#) | [Email](#)


MRS-34-30

### Power Cable Splices, Repair Sleeves and End Seals

#### Product Highlights:

- Repair Sleeve
- MRS Series
- Above Ground Application, Direct Burial Application, Flame Retardant Application, Submersible Application
- Heat Shrinkable Installation Type
- Retention Type = Stainless Steel Retention Channel

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 407236-000


[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information	
<p><b>Product Drawings:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Catalog Pages/Data Sheets:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Product Specifications:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Application Specifications:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Instruction Sheets:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">MRS Flame-retarded Wraparound Sleeve (PDF, English)</a></li> </ul> <p><b>CAD Files:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul>	<p><b>Additional Information:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Product Line Information</a></li> </ul> <p><b>Related Products:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Tooling</a></li> </ul>

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p><b>Product Type Features:</b></p> <ul style="list-style-type: none"> <li>• Product Type = Repair Sleeve</li> <li>• Series = MRS</li> <li>• Retention Type = Stainless Steel Retention Channel</li> <li>• Package = 10 kits/box</li> </ul> <p><b>Mechanical Attachment:</b></p> <ul style="list-style-type: none"> <li>• Installation Type = Heat Shrinkable</li> </ul> <p><b>Dimensions:</b></p> <ul style="list-style-type: none"> <li>• Cable Outer Diameter (mm [in]) = 41.00 - 58.00 [1.600 - 2.300]</li> </ul> <p><b>Body Features:</b></p> <ul style="list-style-type: none"> <li>• Sleeve Length, Nominal (mm [in]) = 750 [30]</li> </ul>	<p><b>Configuration Features:</b></p> <ul style="list-style-type: none"> <li>• Cable Shielding = Without</li> </ul> <p><b>Industry Standards:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">RoHS/ELV Compliance</a> = Not relevant for RoHS and/or ELV compliance</li> <li>• <a href="#">Lead Free Solder Processes</a> = Not relevant for lead free process</li> </ul> <p><b>Printer/Label Features:</b></p> <ul style="list-style-type: none"> <li>• Voltage Rating (kV) = 2</li> </ul> <p><b>Operation/Application:</b></p> <ul style="list-style-type: none"> <li>• Application = Above Ground, Direct Burial, Flame Retardant, Submersible</li> </ul> <p><b>Other:</b></p> <ul style="list-style-type: none"> <li>• Brand = Raychem</li> </ul>

#### Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference Products](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

