

[POWER SYSTEMS](#)

JOINTS & SPLICES



Active

[See All Documentation](#)

TE CONNECTIVITY

MCK-4V

Raychem

MCK

223092-000

TE Internal Number: 223092-000
Alias ID: 8-1191643-7 MCK-4V

Always EU RoHS/ELV Compliant

Product Availability **AMERICAS**

Technology **Heat Shrink**

Voltage Class (kV) ≤ 2

Application **Stub Splice Between 1/C Poly Feeder Cable & Motor Leads. Kits for In-Line Splices Also Available (Type L Kits).**

Product Type **Motor Connection Kit**

[See All Features](#)

DOCUMENTATION

FEATURES

Catalog Pages/Data Sheets

[MCK-MOTOR-CONNECTION-CABLE-ACCESSORIES](#)
PDF
English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

[MCK-XV 1000V Flame-Retarded Motor \(Stub\) Connection Instructions](#)
PDF
English

[MCK-5-XV 5-8kV Class Motor \(Stub\) Connection Instructions](#)
PDF
English

[MCK-5-XL 5-8 KV Class Motor \(In-Line\) Connection Kits Instructions](#)
PDF
English

[MCK-L 1000V Flame-Retarded Motor \(In-Line\) Connection Kits Instructions](#)
PDF
English

[Similar](#)
[View All](#)